



## Silicone elements

### *O-rings*

You can use these O-rings as spacers to keep your beads firmly in place. They are 1 mm thick and flexible, so each ring can fill a space of 0.5 mm – 1 mm.

The O-rings are available in black color.

Dimensions:

internal diameter 1mm, external diameter 3 mm, width 1 mm

### *Silicone tube*

The rods are 1.1 mm thick and your bead probably has a larger hole. For a tight fit you can put silicone tube on the rod. You don't have to put the tube on the full length of the rod just on the two ends of the bead.

The tube is available in black and in transparent version and in two sizes, 2mm and 3 mm.

Dimensions: internal diameter 1mm, external diameter 2 mm or 3 mm

